



Electrical & pneumatic connection box




Flush line

Distribution valve block



Elados diaphragm pumps



Flow meter

Product selection valve block



ULTRAX Compact

The Compact Dispensing Solution for Wash Extractors

MAIN FEATURES

- ◆ Dosing system for up to 8 wash extractors and max 8 products
- ◆ Ecolab *my Control*™ PLC with touch screen display and data management functionalities
- ◆ Two integrated dosing pumps to increase dispensing capacity for bigger machines
- ◆ Compatible with Ecolab Turbo Pump (50 l/h) and Elados Diaphragm Pump (54 l/h)
- ◆ Total volume of water is filtered up to 3 times within one batch cycle
- ◆ Integrated flow meter (Ecolab Oval Gear Meter) for precise metering
- ◆ PP fitting and PEX tubing
- ◆ Resistant to chemicals with pH between 0.8 and 12.0
- ◆ Splash guard and drip tray
- ◆ Compliant with CE, RoHS II and WEEE requirements
- ◆ Flush controlled by the flow meter to avoid mix of different products
- ◆ Wall adapters included in the installation kit
- ◆ PP fitting and PEX tubing

BENEFITS

- ◆ Reduced times of dispensing
 - ◆ Tracking of dispensing quantity of all products
 - ◆ Quick installation by preassembled unit
 - ◆ Space saving
- Dimensions: 1550 mm x 1100 mm x 480 mm

ECOLAB EUROPE GMBH

Richtstrasse 7 · 8304 CH-Wallisellen · Phone +41 44 877 2000

www.ecolab.com

©2013 Ecolab™ USA Inc. All rights reserved.

ECOLAB®

Everywhere It Matters.™